



DEEP REFLECTOR




NANO-X luminous flux

• 800mm	3000K	4.600 Lm	• 800mm	4000K	4.725 Lm
• 1200mm	3000K	6.900 Lm	• 1200mm	4000K	7.425 Lm
• 2400mm	3000K	12.575 Lm	• 2400mm	4000K	13.000 Lm


Comparison of light distribution:

- Louver light distribution is more narrow, around 30° on each side.
- Micro prism offers wider beam, around 45° on each side


Louver ~30° Beam / side



Micro Prism: ~45° Beam / side



ANTI-GLARE LOUVER



• Completely glare free from all viewing angles!


Anti-Glare – luminous flux:

• 800mm	3000K	2.800 Lm	• 800mm	4000K	2.850 Lm
• 1200mm	3000K	4.200 Lm	• 1200mm	4000K	4.500 Lm
• 2400mm	3000K	7.650 Lm	• 2400mm	4000K	7.950 Lm

Anti-Glare
UGR < 17
Less
luminous flux

Comparison of light distribution:

Anti-Glare Screen:



Micro Prism:

